

1

2

3

4

A

B

C




D

A


B

C

D



Circuit Diagram



PCB LAND DIMENSION

SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+85℃

PAPT NO	TS-1159UB-C-A-W
Operating Force	A:100gf B:160gf C:260gf D:320gf E:400gf
Height	H:A:3.5 B:4.3 C:4.9 D:5.2
Color	W:white BL:blue

⑤	Terminal	4	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	PA46		
②	Cover	1	SPSS	Plating Nickel	
①	Keystake	1	Silica gel		
ITEM	PAPT	NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	TACT SWITCH
APPROVED		SIZE: A4	PART NO.: TS-1159UB-C-A-W
			DWG NO.: TS-1159UB-C-A-W
SCALE	PAGE	REVISION	
N/A	1/1	A1	

1

2

3

4