




PCB LAYOUT



Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C~+105°C

温度范围: -40°C~+105°C

Insulation resistance: ≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

X1322	W	V	- 2x06	H	- C40	D30	- E80
①	②	③	④	⑤	⑥	⑦	⑧

1. Series No.

2. Category: W-Water

3. Welding Board Angle: V-Straight 180°

4. Row No -Pin No: 2xXX-2x01P-2x40P

5. Plastic height: J=1.0 mm K=1.5mm I=2.0mm

H=2.5mm D=3.0mm E=3.5mm

F=4.0mm W=5.0mm

6. Pin length: C=4.0mm

7. Pin length: D=3.0mm

8. Pin length: E=(Plastic height + Plastic height+A)

9. Planting Category: Blank=gold plating 1U"

SN=Plating Tin

AuSn=Terminal half-AuSn

V03=Plating 3U"

V15=Plating 15U"

V30=Plating 30U"

X1322WV-2x06H-C40D30-E80	PA6T	Brass	X1321F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector		
DWN		VIEW: 	PART NO.: X1322WV-2x06H-C40D30-E80		
CHKD		UNIT: mm/in	DWG NO.: X-X1322WV-2x06H-C40D30-E80		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED