





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.27	阿树



规格 Specifications:

额定电压 Voltage rating:250VAC/DC.

额定电流 Current rating:1A AC/DC

耐电压 Withstanding voltage:300V AC/minute

温度区间 Temperature range:-40℃to+105℃

绝缘电阻 Insulation resistance:≥500MΩ Min

接触电阻 Contact resistance:≤20MΩ Max

材料 Material: PA6T 94V-0

镀层 Plating Category: 1U"Gold

波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:

X1311 W V-20 J-C18 D27

① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Water
- ③Welding Board Angle:V-Straight 180°
- ④Row No -Pin No:XX-01P-40P
- ⑤Plastic height: J=1.0mm
- ⑥Plastic length:C=2.7mm
- ⑦Plastic length:D=1.8mm

X1311WV-20J-C18D27	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	1.27mm BTB Connector
PART NO.:	X1311WV-20J-C18D27
DWG NO.:	X-X1311WV-20J-C18D27

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1