


P.C.B LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X1270 W V S -2x17 C -6T V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Stright Angle 180°

4.Welding Way:S-SMT


5.Row No-Pin No:2xXX-2x03P~2x32P

6.C:With Horns

7.Material:6T:PA6T UL94V-0

8.Plating Category: V01-All Gold Flash

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
2x03	2.54	18.31
2x04	3.81	19.58
2x05	5.08	20.85
2x06	6.35	22.12
2x07	7.62	23.39
2x08	8.89	24.66
2x09	10.16	25.93
2x10	11.42	27.20
2x12	13.97	29.74
2x13	15.24	31.01
2x15	17.78	33.55
2x17	20.32	36.09
2x20	24.13	39.90
2x25	30.48	46.25
2x30	36.83	52.60
2x32	39.37	55.14



X1270WVS-2x17C-6TV01	PA6T UL 94V-0	Brass	Gold Flash	X1270H-2x17
				X1270H1-2x17
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: Horn type connector		
DWN		VIEW: 	PART NO.: X1270WVS-2x17C-6TV01		
CHKD		UNIT: mm/in	DWG NO.: X-X1270WVS-2x17C-6TV01		
APPD		SIZE: A4	X-X1270WVS-2x17C-6TV01		
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0