



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		新增尺寸, 图面升级整理图面	2025.04.24	阿树





MATERIALS AND FINISH
SHELL: STEEL MATERIAL, FRONT SHELL NICKEL FINISHED
BACK SHELL NICKEL FINISHED
INSULATOR : PBP THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, WHITE COLOR
CONTACT MATERIAL : BRASS
CONTACT FINISH : FULL 3u" GOLD

ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C~+105°C

PART NO.:

X03 25 W C 2 W 4
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Row No-Pin No: XX-09;15;25;37
③Welding Board Angle:W-Male
④C: Car-pin
⑤Planting Category:
1:1u 2:2u 3:3u 4:5u 5:15u 6:30u 7:AuSn
⑥Color: B:Black W:White BL:Blue
Y:Yellow G:Green R:Red
⑦1:TYPE-1; 2:TYPE-2



NO.OF CONTACT	A±0.25	B±0.13	C±0.38	D
09	16.92	24.99	30.81	11.08
15	25.25	33.32	39.14	19.39
25	38.96	47.04	53.04	33.24
37	55.42	63.50	69.32	49.86

铆合方式	TYPE-1: 铆合	TYPE-2: 铆合锁螺丝
图示		

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0325WC2W4
APPROVED		SIZE: A4	DWG NO.: X-X0325WC2W4

SCALE	PAGE	REVISION
N/A	1/1	A1