




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.8.10	阿树




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃~+105℃
温度范围: -40℃~+105℃
Insulation resistance: $\geq 1000M\Omega$
绝缘电阻: $\geq 1000M\Omega$
Contact resistance: $\leq 20m\Omega$ MAX
接触电阻: $\leq 20m\Omega$ MAX

X9555 H2-2x03 C- PT V01
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:H2-three-piece with TYPE1 HSG
- 3.Row No-Pin No:2xXX-2x03P~2x32P
- 4.Special:NO:X Type A or Type B and Type C
- Blank-conventional product
- 5.Material:PT-PBT UL94V-0
- 6.Plating:V01-Gold Flash




14P-64P 双槽



Y型端子

X9555H2-2xXX-PTV01	PBT	BRASS	Gold Flash	X9555WV-2xXX	XPD1.27-A28PXX-IDC	X9555HI-2xXXA
				X9555WR-2xXX		X9555HI-2xXXB
				X9555WVS-2xXX		X9555HI-2xXXC
				X9555WV-2xXX		X9555HI-2xXXA
				X9555WR-2xXX		X9555HI-2xXXB
X9555H2-2xXXX-PTV01				X9555WVS-2xXX		X9555HI-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Wafer	Suitable XKB flat cable	Suitable XKB DIP



6P 小鼻/无槽

TYPE C

6P 大鼻/无槽

TYPE A

8P 大鼻/无槽

TYPE A

6P 小鼻/单槽

TYPE B

8P 小鼻/单槽

TYPE B

10P-12P 单槽

Blank

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
2x03	12.32	5.08	1.9	2x13	37.72	30.48	3.8
2x04	14.86	7.62	小1.9/大3.8	2x15	42.80	35.56	
2x05	17.40	10.16	3.8	2x17	47.88	40.64	
2x06	19.94	12.70		2x18	50.42	43.18	
2x07	22.48	15.24		2x20	55.50	48.26	
2x08	25.02	17.78		2x22	60.58	53.34	
2x09	27.56	20.32		2x25	68.20	60.96	
2x10	30.10	22.86		2x30	80.90	73.66	
2x11	32.64	25.40		2x32	85.98	78.74	
2x12	35.18	27.94					

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.54mm IDC
CHECKED		UNIT:	mm/in	PART NO.:	X9555H2-2x03C-PTV01
APPROVED		SIZE:	A4	DWG NO.:	X-X9555H2-2x03C-PTV01

SCALE	PAGE	REVISION
N/A	1/1	A1