

1



2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚

A




规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: $\leq 30 \text{ m}\Omega$
- 绝缘电阻 Insulation resistance: $\geq 100 \text{ M}\Omega$ (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: $500 \pm 150 \text{ gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

B

5.50 [0.217] 4.00 [0.157] Travel




PART NO.:

SS-X 03 13 P G-10 N 1 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- SS: XKB Vertical handle;
- Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- Current Rating: 03-3A;
- Switch Circuit: 13-1P3T;
- P: Welding plates;
- Handle Shape: G-Camber handle;
- Handle Height: 3~15mm;
- Enclosure Shape: N-Square enclosure;
- Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- Handle Colour:
B-Black; W-White; R-Red
- Housing Colour:
B-Black; W-White; R-Red

C


1.40 [0.055] 4.50 [0.177]



PCB LAYOUT



产品字码标识



D

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-0313PG-10N1BB
APPROVED		SIZE: A4	DWG NO.: X-SS-0313PG-10N1BB
XKB INDUSTRIAL PRECISION CO., LIMITED		SCALE	PAGE
		N/A	1/1
		REVISION	A0

1

2

3

4