

XKB

由 AUTODESK 学生版生成

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V

AC/minute

耐受电压: 800V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

HF-Halogen free

无卤

X2023 W V S-07 -9T SW
① ② ③ ④ ⑤ ⑥ ⑦

①Series No.

②Category:W-WAFER

③Welding Board Angle: V-180°

④Welding Way:S-SMT

⑤Row No.Pin No.: XX-02P-15P;





⑥Material:9T -PA9T 94V-0

⑦Plating Category: SW-Matte Tin

Poles	Dimension mm				Poles	Dimension mm			
	A	B	C	D		A	B	C	D
2	2.00	8.00	4.85	6.00	09	16.00	22.00	18.85	20.00
3	4.00	10.00	6.85	8.00	10	18.00	24.00	20.85	22.00
4	6.00	12.00	8.85	10.00	11	20.00	26.00	22.85	24.00
5	8.00	14.00	10.85	12.00	12	22.00	28.00	24.85	26.00
6	10.00	16.00	12.85	14.00	13	24.00	30.00	26.85	28.00
7	12.00	18.00	14.85	16.00	14	26.00	32.00	28.85	30.00
8	14.00	20.00	16.85	18.00	15	28.00	34.00	30.85	32.00

X2023WVS-07 -9TSW	PA9T UL 94V-0	Brass	Matte Tin	Phorphos Bronze	Matte Tin	X2023H
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Soder Tabs)	Mates With XKB Housing

Recommended P.C.B LAYOUT
Genrd Tolerance±0.05



XKB							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0 mm Crimp Style Connectors				
				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:				
ΔX					L≤4	±0.2	CHKD		DATE		UNIT: mm/in	X2023WVS-07-9TSW				
ΔX					4<L≤16	±0.3		APPD		DATE		SIZE: A4	DWG NO.:			
ΔX					16<L≤63	±0.4								X-X2023WVS-07-9TSW		
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L>63	±0.5								
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.helloxkb.com															1/1	A0