





REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		图面升级整理图面	2025.02.26
A2	N/A		产品电气性能变更	2025.12.23



规格 Specifications:
额定电压 Voltage rating:500VAC/DC.
额定电流 Current rating:2A AC/DC
耐电压 Withstanding voltage:500V AC/minute
温度区间 Temperature range:-40℃to+125℃
绝缘电阻 Insulation resistance:≥1000MΩ Min
接触电阻 Contact resistance:≤20MΩ Max
材料 Material: PA6T UL94V-0
镀层 Plating Category: 1U"Gold
波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:

X4622 W R-2x09 K L-C13 D50
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No.Pin No:2xXX-2x01~2x40P
- ⑤Plastic height: K=1.5mm
- ⑥L-Type L
- ⑦Plastic length: C=1.3mm
- ⑧Plastic length: D=5.0mm

X4622WR-2x09KL-C13D50	PA6T UL94V-0	Brass	1U"Gold	X4622F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female
DESIGN	阿树	VIEW:	MODEL TYPE: 2.0mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X4622WR-2x09KL-C13D50	
APPROVED		SIZE: A4	DWG NO.: X-X4622WR-2x09KL-C13D50	
SCALE			PAGE	REVISION
N/A			1/1	A2

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED