


- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ



- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: XX-02P~20P
- ⑤ Piug the Pin\$ Special No.:K-KINK
- ⑥ Material : N0-PA66;46-PA46 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating

X8821WV-02K-46SN	PA46 UL 94V-0	Brass	Tin-Plated	X8821H
X8821WV-02K-N0SN	Nylon 66 UL 94V-0			
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

					ANGLAR	±5°	DWN		DATE		VIEW: 	2.5mm Crimp Style Connectors				
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	PART NO.: X8821WV-02K-N0SN				
Δx					4<L ≤ 16	±0.3			DATE				DWG NO.:			
Δx					16<L ≤ 63	±0.4			DATE				X-X8821WV-02K-N0SN			
MARK	DESCRIPTION				DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4				
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT	SHEET	REVISION		
													1/1	A0		