

1


2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚

16.20 [0.638]




10.50 [0.413]

5.50 [0.217]


4.00 [0.157] Travel

3.30 [0.130]



产品凸码标识

8.50 [0.335]



4.00 [0.157]

规格 Specification:

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles

5.操作力 Operation force:500±150gf

6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 12 S G-12 N 2 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS: XKB Vertical handle;

② Enclosure Material:

A-Metal case;

BLANK-Plastic case;

③ Current Rating: 03-3A;

④ Switch Circuit:12-1P2T;

⑤ S: Wire bonding;

⑥ Handle Shape: G-Camber handle;

⑦ Handle Height: 3~15mm;

⑧ Enclosure Shape:N-Square enclosure;

⑨ Terminal specs:

1:TYPE-1; 2:TYPE-2; 3:TYPE-3;

4:TYPE-4; 5:TYPE-5;

⑩ Handle Colour:

B-Black; W-White; R-Red

⑪ Housing Colour:


B-Black; W-White; R-Red

XKB 3A 125/250VAC


SS Series
3A 125/250VAC

产品字码标识

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



CIRCUIT



XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN

桑 葚

VIEW:

MODEL TYPE:
SLIDE SWITCH

CHECKED

UNIT: mm/in

PART NO.:

APPROVED

SIZE: A4

DWG NO.:

X-SS-0312SG-12N2BB

SCALE

PAGE

REVISION

N/A 1/1 A0

1

2

3

4