



| REVISIONS |                  |          |             |            |        |
|-----------|------------------|----------|-------------|------------|--------|
| REV.      | ECN NO.          | LOCATION | DESCRIPTION | DATE       | DESIGN |
| A1        | N/A              |          |             | 2025.12.22 |        |
| A2        | ECN-P-2026030301 | ②X1      |             | 2026.03.03 |        |



02P

03~06P




■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥ 1000MΩ
- Contact resistance:≤20mΩ

PART NO.:


X9357 W R-06 S-N2 SN

Series No  
Category:W-Wafer  
Welding Board Angle:R-Stright 90°  
Row No.Pin No:XX-02~06Pin  
Special NO.: S-With positioning column  
Material:N0-PA66 94V-0; N2-PA66 94V-2  
Planting:SN-Bright tin plating;V30-Gold 30u”



P.C.B. Layout  
02P

P.C.B. Layout  
03~06P



| Poles | Dimensions(mm) |       |
|-------|----------------|-------|
|       | A              | B     |
| 02    | 4.20           | 9.80  |
| 03    | 8.40           | 14.00 |
| 04    | 12.60          | 18.20 |
| 05    | 16.80          | 22.40 |
| 06    | 21.00          | 26.60 |

|                   |                   |               |             |                      |
|-------------------|-------------------|---------------|-------------|----------------------|
| X9357WR-06S-N0SN  | Nylon 66 UL 94V-0 | Brass         | Tin-Plated  | X9357H               |
| X9357WR-06S-N2SN  | Nylon 66 UL 94V-2 |               | Gold-Plated |                      |
| X9357WR-06S-N2V30 |                   |               |             |                      |
| PART NO           | Material          | Material(Pin) | Finish(Pin) | Suitable XKB Housing |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |             |                                           |
|----------|-------------|-------------------------------------------|
| DESIGN   | VIEW:       | MODEL TYPE: 4.20 mm Crimp Style Connector |
| CHECKED  | UNIT: mm/in | PART NO.: X9357WR-06S-N2SN                |
| APPROVED | SIZE: A4    | DWG NO.:                                  |