

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		尺寸变更	2024.8.20	阿树
A2	N/A		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.7	阿树

PART NO.:





X05 15 F C 2 W 1
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Pin No.:15PIN
③Welding Board Angle :F-Female
④T: Tradutlional C: Car-pin
⑤Planting Catogtry:
1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AU SN
⑥Color:B-BLACK W-White BL-Blue
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7


Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
2.Current rating:3A(T) / 5A(C) AC/DC
额定电流: 3A(冲针) / 5A(车针) AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
4.Temperature range: -55℃-+105℃
温度范围: -55℃-+105℃
5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ
Material:
材料:
7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
8.Terminal:Copper alloys
端子: 铜合金。
9.The iron shell:SPCC Nivkel Plating/
Tin Plating/Gold Plating
铁壳: SPCC,镀镍/镀锡/镀金
B、成品不能有弯针, R角不一致等不良。



PCB LAYOUT



AUGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	D-SUB
PART NO.:	X0515FC2W1
DWG NO.:	X-X0515FC2W1