








Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 100M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing: $\leq 40m\Omega$

X1002 H- 02- A- N0 HF
① ② ③ ④ ⑤ ⑥

- ① Series No.
② Category : H-HSG
③ Row No.Pin No.XX-02P-20P
④ Plug the Pin & Special No:A-Ultra-thin
⑤ Material:N0-PA66 94V-0
⑥ HF-Halogen Free

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	1.00	3.00	2.40	12	11.00	13.00	12.40
03	2.00	4.00	3.40	13	12.00	14.00	13.40
04	3.00	5.00	4.40	14	13.00	15.00	14.40
05	4.00	6.00	5.40	15	14.00	16.00	15.40
06	5.00	7.00	6.40	16	15.00	17.00	16.40
07	6.00	8.00	7.40	17	16.00	18.00	17.40
08	7.00	9.00	8.40	18	17.00	19.00	18.40
09	8.00	10.00	9.40	19	18.00	20.00	19.40
10	9.00	11.00	10.40	20	19.00	21.00	20.40
11	10.00	12.00	11.40				

X1002H-02A-N0HF	PA66 UL 94V-0 Halogen Free	X1002T-A
PART NO	Material	Suitable X K BTerminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connectors		
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:		
Δx					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	X1002H-02A-N0HF		
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4	DWG NO.:		
MARK	DESCRIPTION			DATE	REVISED	APPROVED		L>63	±0.5				X-X1002H-02A-N0HF	
REVISIONS							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
UNSPECIFIED TOLERANCES												1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														