


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.8	阿树



Temperature range: -40°C - +125°C
温度范围: -40°C - +125°C

PART NO.:
K 776280 H-23-PT GY
① ② ③ ④ ⑤ ⑥
①K:XKBTEK-Car Connector
②XKB Series No
③Category:H-Housing
④Row No.Pin No:23 Pin
⑤Material:PT-PBT
⑥Color:X:B-Black;

5	Terminal locks	Red	PBT	1
4	Rubber rings	Brown	Silica gel	1
3	Housing	Black	PBT	1
2	Rubber plugs	Green	Silica gel	1
1	Cover	Black	PBT	1
NO	NAME	COLOR	MATERIAL	QTY

K776280H-23-PTGY	PBT	K776280W	K776280T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	4.0mm Automobile connector
PART NO.:	K776280H-23-PTGY
DWG NO.:	X-K776280H-23-PTGY

SCALE	PAGE	REVISION
N/A	1/1	A1