


Specifications:
规格:
Voltage rating:30V AC/DC
额定电压: 30V AC/DC
Current rating: 0.2A AC/DC
额定电流: 0.2A AC/DC
Withstanding voltage:200V AC/minute
耐压电压: 200V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤30mΩ
接触电阻:≤30mΩ

X0600 WRS - 05 - LP V01 HF

① ②③④ ⑤ ⑥ ⑦ ⑧

- ①Series No.
②Category: W-wafer
③Welding Board Angle: R-90°
④Row No.-Pin No.: XX-Single row
⑤Material: LP-LCP 94V-0
⑥Planting Category : V01-All Gold Flash
⑦Plug the Pin & Special NO.:HF-Halogen Free

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	0.60	3.00	12	6.60	9.00
3	1.20	3.60	13	7.20	9.60
4	1.80	4.20	14	7.80	10.20
5	2.40	4.80	15	8.40	10.80
6	3.00	5.40	16	9.00	11.40
7	3.60	6.00	17	9.60	12.00
8	4.20	6.60	18	10.20	12.60
9	4.80	7.20	19	10.80	13.20
10	5.40	7.80	20	11.40	13.80
11	6.00	8.40	22	12.60	15.00



Recommended P.C.B Layout
General Tolerance±0.05

X0600WRS-05-LPV01HF	LCP	Phosphor Bronze	X0600WRS
PART NO	Material	Material(Pin)	Suitable XKB Housing

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
MARK					
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 0.6mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X0600WRS-05-LPV01HF		
CHKD		UNIT: mm/in	DWG NO.: X-X0600WRS-05-LPV01HF		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0