





HSF



ROHS



PCB LAYOUT



SPECIFICATION

Current Rating:	3Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PBT,UL 94V-0 Black

Ordering Code:

PHES07 - X - X - D - A - C - B - X - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No:
② No. of Contacts
02 To 80
③ Contact Plating:
G0:Gold flash S0:Selective
G1:3u" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin
④ Connector Type
D:Dual
⑤ Pin Length:
A:0600=6.00mm
C:0675=6.75mm
B:0300=3.00mm
Please mark the desired length in the A/C/B
⑥ Insulator Material
A:PBT
B:PA6T
C:LCP
D:PA46
E:PA9T
⑦ Packing:
A:Tray
B:Bag
T:Tube
U:Tube+CAP
R:Tape&Reel
W:Tape&Reel+CAP
⑧ Shape option
A: Type 1
B: Type 2
⑨ Plastic High
H1:1.7mm
H2:2.54mm
H3:2.00mm
H4:1.50mm

Standard IE P/N :

PHES07-06-G0-D-0300-0508-0300-B-B-A-H2

A	C	B	Unless Otherwise specified tolerance	
6.00	6.75	3.00	X. ±0.35	X.XX: ±0.20
			X.X: ±0.25	X.XXX: ±0.15
Optional		SCALE: As Shown	UNIT: mm	
		DRAW YG ZHONG	DATE 01/05/2016	
		CHECK BobYang	DATE 01/05/2016	



ANTENK ELECTRONICS CO.,LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE:
2.54mm Pin Header DualRow Double Plastic Straight Type

DRAWING NO: PHES07-06-G0-D-0300-0508-0300-B-B-A-H2

PRODUCT NO: PHES07-06-G0-D-0300-0508-0300-B-B-A-H2



REV

ADD H4=1.5MM
Increase packing method and material

DESCRIPTION

DATE