




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance: 1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X2001 H - 2x11 -PT V01
① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-Two-piece
- 3.Row No.Pin No:2xXX-2x03-2x25P
- 4.Material:PT-PBT Glass Fiber UL94V-0
- 5.Plating:V01-Gold Flash

Poles	DIM A	DIM B
2x03	4.00	11.20
2x04	6.00	13.20
2x05	8.00	15.20
2x06	10.00	17.20
2x07	12.00	19.20
2x08	14.00	21.20
2x09	16.00	23.20
2x10	18.00	25.20
2x11	20.00	27.20
2x12	22.00	29.20
2x13	24.00	31.20
2x14	26.00	33.20
2x15	28.00	35.20
2x17	32.00	39.20
2x18	34.00	41.20
2x20	38.00	45.20
2x22	42.00	49.20
2x25	48.00	55.20

X2001H-2x11-PTV01	PBT Glass Fiber	Brass	X2001W-A/X2001W-D
PART NO	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	2.0mm IDC Connector
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	X2001H-2x11-PTV01
			DWG NO.:
			X-X2001H-2x11-PTV01
WEIGHT		SHEET	REVISION
		1/1	A0