




Recommended PCB Layout
General Tolerance±0.05

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/ 分钟

Temperature range:-25 ℃ -+85℃

温度范围: -25℃ -+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X2011 W V 02 A -NO SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:Blank-DIP

5.Row No-Pin No:XX-02P~16P

6.Plug the Pin&Special No:A-Without Baffle

7.HF-Halogen Free

8.Material:NO-PA66 UL 94V-0;LCP 94V-0

9.Plating Category:SN-Bright Tin Plating
SW-Matte Tin Plating

10.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2	2.00	6.00	4.75	10	18.00	22.00	20.75
3	4.00	8.00	6.75	11	20.00	24.00	22.75
4	6.00	10.00	8.75	12	22.00	26.00	24.75
5	8.00	12.00	10.75	13	24.00	28.00	26.75
6	10.00	14.00	12.75	14	26.00	30.00	28.75
7	12.00	16.00	14.75	15	28.00	32.00	30.75
8	14.00	18.00	16.75	16	30.00	34.00	32.75
9	16.00	20.00	18.75				

X2011WV-02A-LPSW	LCP 94V-0	Brass	Matte Tin-Plated	X2011H
X2011WV-02AHF-N0SN	PA66 UL 94V-0 Halogen Free		Tin-Plated	
X2011WV-02A-N0SN	PA66 UL 94V-0			
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors		
						units:	mm	DWN		VIEW:	PART NO.: X2011WV-02A-NOSN		
						tolerance:		CHKD		UNIT: mm/in	DWG NO.: X-2011WV-02A-NOSN		
						X.X	±0.2mm	APPD		SIZE: A4			
						X.XX	±0.1mm						
						X.XXX	±0.05mm						
MARK	DESCRIPTION	DATE	REVISED	APPROVED		UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
REVISIONS											WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1.0g	1/1	A0