


Recommand PCB Layout

SpecificationsXKB

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC XKB

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃--+85℃

温度范围: -25℃--+85℃

Insulation resistance:≥1000MΩ





绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ XKB

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧



X9556 W R -17-N0V01

- 11 Series No.
12 Category :
W-wafer
13 Welding Board Angle:
R-90°
14 Welding Way:
Blank-DIP
15 Row No.-Pin No.
XX-Single row
16 Special NO.
17 Material :
N0-PA66 94V-0
18 Planting Category:
V**All Gold-Plated
"01-1u" ; "02-2u" ; "03-3u" ; "05-5u"
"10-10u" ; "15-15 u" ; "30-30u" ; "50-50u"
SN-Bright tin plating 70U"
SN1-Bright tin plating 120U"Min. ;
SW-Fog Tin plating
19 Color:
Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	2.54	7.62
3	5.08	10.16
4	7.62	12.70
5	10.16	15.24
6	12.70	17.78
7	15.24	20.32
8	17.78	22.86
9	20.32	25.40
10	22.86	27.94
11	25.40	30.48
12	27.94	33.02
13	30.48	35.56
14	33.02	38.10
15	35.56	40.64
16	38.10	43.18
17	40.64	45.72
18	43.18	48.26
19	45.72	50.80
20	48.26	53.34
21	50.80	55.88
22	53.34	58.42
23	55.88	60.96
24	58.42	63.50

X9556WR-17-N0V01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X9556H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

XKB						DSND		DATE		SCALE: N/A	MODEL TYPE:			
				XKB	ANGLAR	±5°	DWN		DATE	VIEW: 	2.54 mm Crimp Style Connectors			
Δx					L≤4	±0.2	CHKD		DATE	UNIT: mm/in	PART NO.:			
Δx					4<L≤16	±0.3		X9556WR-17-N0V01						
Δx					16<L≤63	±0.4		DWG NO.:						
MARK	DESCRIPTION			DATE	REVISED	APPROVED	APPD		DATE	SIZE: A4	X-X9556WR-17-N0V01			
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.helloxkb.com						1.0g						1/1	A0	