






04P~20P Shape
Scale 1:1



02P~03P Shape
Scale 1:1

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X3535 H -02 -N0

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:H-HSG

3.Appearance type:Blank-Ordinary

4.Row No-Pin No:XX-02P~20P

5.Plug the Pin&Special N0:

Blank-Ordinary

6.Material:N0-PA66 UL 94V-0

7.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2	2.00	7.30	5.10	10	18.00	22.30	21.10	18	34.00	38.30	37.10
3	4.00	9.30	7.10	11	20.00	24.30	23.10	19	36.00	40.30	39.10
4	6.00	10.30	9.10	12	22.00	26.30	25.10	20	38.00	42.30	41.10
5	8.00	12.30	11.10	13	24.00	28.30	27.10				
6	10.00	14.30	13.10	14	26.00	28.30	29.10				
7	12.00	16.30	15.10	15	28.00	32.30	31.10				
8	14.00	18.30	17.10	16	30.00	34.30	33.10				
9	16.00	20.30	19.10	17	32.00	36.30	35.10				

X3535H-02-N0	PA66 UL 94V-0	X3535T	X3535W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X3535H-02-N0
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3535H-02-N0
APPD		DATE		SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

					units: mm
ΔX					tolerance:
ΔX					X.X ±0.2mm
ΔX					X.XX ±0.1mm
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm
REVISIONS					UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					