




■ SPECIFICATIONS

- Voltage rating:250V AC,DC
- Current rating:3A,AC,DC
- Withstanding Voltage:800V AC/minute
- Insulation resistance:1000MΩ min
- Temperature range:-45°C+95°C
- Contact resistance:20mΩ max

PART NO.:

<u>K</u>	<u>202820</u>	<u>W</u>	<u>V-2x20</u>	<u>S-N0</u>	<u>SN</u>
①	②	③	④	⑤	⑥ ⑦ ⑧

- ①K:XKBTEK—Car Connector
- ②XKB Series No
- ③Category:W—Wafer
- ④Welding Board Rangle:V—Stright 180°
- ⑤Row No.—Pin No:2xXX—2x04P~2x21P
- ⑥S—With registrarion mast;
blank—without registration
- ⑦Material:NO—PA66 UL 94V—0
- ⑧Plating Category: SN—Tin—Plated



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		INITIAL RELEASE	2024.7.13	阿树
A2	N/A		更新图框	2024.12.27	阿树

Poles	Dimension mm	
	A	B
2x04	6.00	10.00
2x05	8.00	12.00
2x06	10.00	14.00
2x07	12.00	16.00
2x08	14.00	18.00
2x09	16.00	20.00
2x10	18.00	22.00
2x11	20.00	24.00
2x12	22.00	26.00
2x13	24.00	28.00
2x14	26.00	30.00
2x15	28.00	32.00
2x16	30.00	34.00
2x17	32.00	36.00
2x18	34.00	38.00
2x19	36.00	40.00
2x20	38.00	42.00
2x21	40.00	44.00

K202820WV-2x20S-NOSN	PA66	Brass	Tin-Plated	K202820H	2x18	34.00	38.00
PART NO	Material	Material (pin)	Flinish(pin)	Suitable XKB Housing	2x19	36.00	40.00
					2x20	38.00	42.00
					2x21	40.00	44.00
		DESIGN	阿树	VIEW: 	MODEL TYPE: 2.0mm Automobile Connector		
		CHECKED		UNIT: mm/in	PART NO.: K202820WV-2x20S-NOSN		
		APPROVED		SIZE: A4	DWG NO.: X-K202820WV-2x20S-NOSN		
XKB INDUSTRIAL PRECISION CO.,LIMITED					SCALE N/A	PAGE 1/1	REVISION A2