




AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAuCES	



3.1: CURRENT RATING:0.5A/PIN
3.2: VOLTAGE RATING:50V (AC/DC)
3.3:CONTACT RESISTANCE:INITIAL VALUE 30mOHM MAX.
3.4:INSULATOR RESISTANCE:500mOHM in.
3.5:DIELECTRIC WITHSTANDING VOLTAGE:250V AC FOR 1MINUTE
3.6: DURABILITY: 20 TIMES Min.
3.7:OPERATING TEMPERATURE:-40℃+85℃
OPERATING HUMIDITY RANGE: 20% TO 85%

Reinforcing Layer

RECOMMENDED	FFC	DIM
-------------	-----	-----

300 [0119]MIN

Rein

Reinforcing Layer

VIEW: 

UNIT: mm/in

SIZE: A4

MODEL TYPE:	FPC CONNECTOR
-------------	---------------

n	PART NO.: X10B25U18G
---	-------------------------

DWG NO.:	Y10B25U18G
----------	------------

SCALE	PAGE	REVISION
N/A	1/1	A1