





Mating PCB detail



Assembly Layout


Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 7A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X9396 W V S-06- 9T SN

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.XX-Single row
- ⑥ Material:9T-PA9T 94V-0
- ⑦ Planting Category:SN-Bright tin plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	3.96	11.88	8.60	093	1.68	39.60	36.32
03	7.92	15.84	12.56	103	5.64	43.56	40.28
04	11.88	19.80	16.52	11	39.60	47.52	44.24
05	15.84	23.76	20.48	12	43.56	51.48	48.20
06	19.80	27.72	24.44	13	47.52	55.44	52.16
07	23.76	31.68	28.40	14	51.48	59.40	56.12
08	27.72	35.64	32.36	15	55.44	63.36	60.08



X9396WVS-02

X9396WVS-03

X9396WVS-06-9TSN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9396H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable X K B Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE:			
						ANGLAR	±5°	DWN		DATE	VIEW: 	3.96mm Crimp Style Connectors			
ΔX						L ≤ 4	±0.2					PART NO.:			
ΔX						4<L ≤ 16	±0.3	CHKD		DATE		X9396WVS-06-9TSN			
ΔX						16<L ≤ 63	±0.4				UNIT: mm/in	DWG NO.:			
MARK	DESCRIPTION				DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4	X-X9396WVS-06-9TSN		
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															
										1.0g 1/1 A0					