




P.C.B LAYO UT

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω

X3025W V - 02C-LPSN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Series No.

② Category :

W-wafer

③ Welding Board Angle:

V-180°

④ Welding Way:

Blank-DIP

⑤ Row No.-Pin No.

XX-Single row

⑥ Special NO.

C-With a harpoon

⑦ Material :

LP-LCP 94V-0 66-PA66 94V-0

⑧ Planting Category:

V**:All Gold-Plated

G**:Gold-Plated Contact

*01-Gold Flash ; *02-2u" ; *03-3u" ; *05-5u"

*10-10u" ; *15-15u" ; *30-30u" ; *50-50u"

SN-Bright tin plating 70u"

SN1-Bright tin plating 120u"Min. ;

SW-Fog Tin plating

⑨ Color:

Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
9	24.00	30.65
10	27.00	33.65
11	30.00	36.65
12	33.00	39.65

X3025WV-02C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WV-02C-LPSN	LCP UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

				XKB	ANGLAR	±5°
ΔX					L≤4	±0.2
ΔX					4<L≤16	±0.3
ΔX					16<L≤63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L>63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com						

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
DWN		DATE		VIEW: 	PART NO.: X3025WV-02C-XXSN		
CHKD		DATE		UNIT: mm/in	DWG NO.: X3025WV-02C-XXSN		
APPD		DATE		SIZE: A4			
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
					1.0g	1/1	A0