





4PIN以上



2PIN和3PIN



Recommend PCB Layout

X2508 W V - 07 - N0 SN

① ②③④ ⑤⑥ ⑦ ⑧ ⑨

- ①系列
②类别: W-WAFER类
③外观形态:
V-180°
④成型方式:
空码-DIP
⑤PIN数:
单排-XX
⑥空PIN位置及特殊码
⑦材质:
N0-PA66 94V-0 N2-PA66 94V-2
⑧电镀类别:G**-镀金 V**-镀全金
*O1-1U" *O2-2U" *O3-3U" *O5-5U"
*10-10U" *15-15U" *30-30U" *50-50U"
SN-镀亮锡(70-120U") SN1-镀亮锡(120U"Min.)
SW-镀雾锡 HS-高温锡
⑨颜色:
空码-本色或普通色

Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage: 1500V AC/minute
耐压电压: 1500V AC/minute
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance: ≤10Ω
接触电阻:≤10Ω
After environmental testing:≤20mΩ
环境测试后: ≤20mΩ

Poles	Dimensions(mm)		
	A	B	C
2	7.50	5.8	2.50
3	10.00	8.3	5.00
4	12.50	10.8	7.50
5	15.00	13.3	10.00
6	17.50	15.8	12.50
7	20.00	18.3	15.00
8	22.50	20.8	17.50
9	25.00	23.3	20.00
10	27.00	25.80	22.50
11	12.50	28.30	25.00
12	15.00	30.80	27.50
13	17.50	33.30	30.00
14	20.00	35.80	32.50
15	22.50	38.30	35.00

X2508WV-07-N0SN	Nylon 66 UL 94V-0	Brass	Tin Plated	X2508H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.50 mm Crimp Style Connectors						
Δx						ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2508WV-07-N0SN					
Δx						L≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2508WV-07-N0SN					
Δx						4<L≤ 16	±0.3	APPD		DATE		SIZE: A4						
Δx						16<L≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT	SHEET	REVISION		
MARK	DESCRIPTION				DATE	REVISED	APPROVED							L> 63	±0.5	1.0g	1/1	A0
REVISIONS							UNSPECIFIED TOLERANCES											
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																		