






Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥100MΩ

绝缘电阻: ≥100MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X9357 W V- 2x04 - N2 SN
① ② ③ ④ ⑤ ⑥

1.Series No.



2.Category:W-Wafer

3.Welding Board Angle: V- Stright 180°

4.Row No.Pin No:2xXX-2x01P~2x12P

5.Material: N0-PA66 94V-0:N2-PA66 94V-2

6.Plating Category: SN-Bright Tin Plating
V01-Plating Gold Flash



Recommended P.C.B Layout

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	5.40	—	2*07	30.60	25.20
2*02	9.60	4.20	2*08	34.80	29.40
2*03	13.80	8.40	2*09	39.00	33.60
2*04	18.00	12.60	2*10	43.20	37.80
2*05	22.20	16.80	2*11	47.40	42.00
2*06	26.40	21.00	2*12	51.60	46.20

X9357WV-2x04-N2SN	PA66 UL94V-2	Brass	X9357HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

						XKB	DSND		DATE		SCALE: N/A	MODEL TYPE:
				XKB	ANGLAR	±5°	DWN		DATE		VIEW:	4.2 mm Crimp Style Connectors
ΔX					L≤4	±0.2	CHKD		DATE		UNIT: mm/in	PART NO.:
ΔX					4<L≤16	±0.3	APPD		DATE		SIZE: A4	X9357WV-2x04-N2SN
ΔX					16<L≤63	±0.4						DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L>63	±0.5						X-X9357WV-2x04-N2SN
REVISIONS						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.helloxkb.com										1.0g	1/1	A0