



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.06.10	阿树
A2	ECN-P-2025112903	ⒶX1	根据实物变更尺寸	2025.11.29	阿树




X2540-B 2 GF B

COLOR:
B:BLACK
GF:Gold flash

HEIGHT:
2:4.5mm

HOUSING TYPE:
B:CLOSE



SPECIFICATIONS

Contact Resistance: 3 aperes Max

Current Rationg: 3m Max

Insulator Resistance:1000 Megohms Max

Dielectric Withstanding Voltage: AC 650 Volts RMS at sealeve

Materia:

Terminal:Brass

Housing:PBT

Dimen Sions List

Contacts Per row	Dimensions	
	A	B
1	2.00	
2	4.00	2.00
3	6.00	4.00
4	8.00	6.00
5	10.00	8.00
6	12.00	10.00
7	14.00	12.00
8	16.00	14.00
9	18.00	16.00
10	20.00	18.00

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.54 CONN
CHECKED		UNIT:	mm/in	PART NO.:	X2540-B2GFB
APPROVED		SIZE:	A4	DWG NO.:	