





■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 10\text{m}\Omega$
- After environmental testing : $\leq 20\text{m}\Omega$
- Mark ""Indica te Dimensions Need To Controlled In Emphasis



X3025 W V S- 03 C-LPSW

- | | | | | | | | | | |
|----|--|----|----|----|----|----|----|----|----|
| | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 |
| 11 | Series No. | | | | | | | | |
| 12 | Category : | | | | | | | | |
| | W-wa fer | | | | | | | | |
| 13 | Welding Board Angle: | | | | | | | | |
| | V-180° | | | | | | | | |
| 14 | Welding Way: | | | | | | | | |
| | S-SMT | | | | | | | | |
| 15 | Row No.-Pin No. | | | | | | | | |
| | XX-Single row | | | | | | | | |
| 16 | Special NO. | | | | | | | | |
| | C-The harPoon | | | | | | | | |
| 17 | Material: | | | | | | | | |
| | LP-LCP 94V-0 66-PA66 94V-0 | | | | | | | | |
| 18 | Planting Category: | | | | | | | | |
| | V***All Gold-Plated | | | | | | | | |
| | G***Gold-Plated Contact | | | | | | | | |
| | *01-Gold Flash ; *02-2U" ; *03-3U" ; *05-5U" | | | | | | | | |
| | *10-10U" ; *15-15U" ; *30-30U" ; *50-50U" | | | | | | | | |
| | SN-Bright tin plating 70U" | | | | | | | | |
| | SN1-Bright tin plating 120U"Min. ; | | | | | | | | |
| | SW-Fog Tin plating | | | | | | | | |
| 19 | Color : | | | | | | | | |
| | Blank-natural color | | | | | | | | |

Poles	Dimensions (mm)		
	A	B	C
02	6.85	3.00	7.30
03	9.85	6.00	10.30
04	12.85	9.00	13.30
05	15.85	12.00	16.30
06	18.85	15.00	19.30
07	21.85	18.00	22.30
08	24.85	21.00	25.30
09	27.85	24.00	28.30
10	30.85	27.00	31.30
11	33.85	30.00	34.30
12	36.85	33.00	37.30

X3025 WVS-03C-LPSW	LCP UL 94V-0	Brass	Tin Plating Fog	Brass	Tin-Plated	X3025H
X3025WVS-03C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	Brass	Tin-Plated	X3025H
PART NO	Material	Material(pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
Δx				XKB	ANGLAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X3025WVS-03C-LPSW		
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025WVS-03C-LPSW		
Δx					$4 < L \leq 16$	± 0.3								
Δx					$16 < L \leq 63$	± 0.4								
MARK	DESCRIPTION			DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4			
REVISIONS							UNSPECIFIED TOLERANCES							
www.helloxkb.com							XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0