




Right Angle Type




Voltage rating:500V AC/DC
额定电压 :500V AC/DC
Current rating:1.0A
额定电流: 1.0A
Insulation resistance:1000MΩ Min
绝缘电阻: 1000MΩ Min
Withstanding voltage:≥500V AC/minute
耐压: ≥500VC/分钟
Temperature range:-40℃-+105℃
使用温度: -40℃-+105℃

X1270 W R -2x30 A2 - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:W-wafer
- ③ Welding Board Angle:R- Straight 90°
- ④ Row No.-Pin No.:2xXX-2x03P~2x40P
- ⑤ A2:1.27x2.54mm No gaps
- ⑥ Material:PT-Nylon PA6T UL94V-0
- ⑦ Planting Category:V01-All Gold Flash



P.C.B Layout



positor	A	B	C
2x03	11.37	9.77	2.54
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x09	18.99	17.39	10.16
2x10	20.26	18.66	11.43
2x12	21.53	19.93	12.70
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53

X1270WR-2x30A2-6TV01	PA6T UL 94V-0	Brass	Gold Flash	X1270HA2-30B
				X1270HA2-30A
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

	DSND		SCALE: N/A	MODEL TYPE: 1.27x2.54mmJane cattle简牛		
	DWN		VIEW: 	PART NO.: X1270WR-2x30A2-6TV01		
	CHKD		UNIT: mm/in	DWG NO.: X-X1270WR-2x30A2-6TV01		
	APPD		SIZE: A4			
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
					1/1	A0