






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.1.4	阿树
A2	N/A	Ⓐ2 X2	产品尺寸及电气性能变更	2025.09.10	阿树



PART NO.:

X9357 W V-2x08 HN-N2 SN XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Row No.Pin No:2xXX-2x01P~2x12P
- ⑤Plug the Pln&Specal NO.:HN-The hollow needle
- ⑥Material:N0-PA66 94V-0;
N2-PA66 94V-2
- ⑦Planting: SN-Bright tin plating
- ⑧Color:Blank-natural color;;B-Black

SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:7A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-40°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

Poles	Dimensions(mm)	
	A	B
2x01	—	5.60
2x02	4.20	9.80
2x03	8.40	14.00
2x04	12.60	18.20
2x05	16.80	22.40
2x06	21.00	26.60
2x07	25.20	30.80
2x08	29.40	35.00
2x09	33.60	39.20
2x10	37.80	43.40
2x11	42.00	47.60
2x12	46.20	51.80

X9357WV-2x08HN-N2SN1	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
X9357WV-2x08HN-N2SNB	Nylon 66 UL 94V-2 Black			
X9357WV-2x08HN-N2SN	Nylon 66 UL 94V-2			
X9357WV-2x08HN-N0SN	Nylon 66 UL 94V-0			
PARE NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	4.20 mm Crimp Style Connectors
APPROVED		SIZE: A4	PART NO.:
			X9357WV-2x08HN-N2SN
			DWG NO.:
			X-X9357WV-2x08HN-N2SN

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2