







Recommended PCB Layout
Total tolerance:±0.05mm



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max

X3025 W R - 04 - 9T SN
① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:R-Stright 90°

4.Row No.Pin No:XX-02~12P

5.Material:9T-PA9T UL94V-0

6.Plating:SN-Tin Plated over Nickel

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	3.00	9.65	8	21.00	27.65
3	6.00	12.65	9	24.00	30.65
4	9.00	15.65	10	27.00	33.65
5	12.00	18.65	11	30.00	36.65
6	15.00	21.65	12	33.00	39.65
7	18.00	24.65		0.00	0.00

X3025WR-04-9TSN	PA9T	Brass	X3025HM
PART N0	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
△X					L ≤ 4	±0.2
△X					4<L ≤ 16	±0.3
△X					16<L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X3025WR-04-9TSN		
CHKD		UNIT: mm/in	DWG NO.: X-X3025WR-04-9TSN		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0