





Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X2026 W R -2x09B-N0SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:R-Right Angle 90°

4.Welding Way:Blank-DIP

5.Row No-Pin No:2xXX-2x02P~2x22P


6.Plug the Pin&Special N0:

B-With Lock In the middle


7.Material:N0-PA66 94V-0

8.Plating Category:SN-Bright Tin Plating



9.Color:Blank-Natural Color



05P~13P Shape(Scale1:1)



02P~04P Shape(Scale1:1)



Recommended PCB Layout
General Tolerance±0.05

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	6.00	4.70	2x10	18.00	22.00	20.70	2x18	34.00	38.00	36.70
2x03	4.00	8.00	6.70	2x11	20.00	24.00	22.70	2x19	36.00	40.00	38.70
2x04	6.00	10.00	8.70	2x12	22.00	26.00	24.70	2x20	38.00	42.00	40.70
2x05	8.00	12.00	10.70	2x13	24.00	28.00	26.70	2x21	40.00	44.00	42.70
2x06	10.00	14.00	12.70	2x14	26.00	30.00	28.70	2x22	42.00	46.00	44.70
2x07	12.00	16.00	14.70	2x15	28.00	32.00	30.70	2x23	44.00	48.00	46.70
2x08	14.00	18.00	16.70	2x16	30.00	34.00	32.70	2x24	46.00	50.00	48.70
2x09	16.00	20.00	18.70	2x17	32.00	36.00	34.70	2x25	48.00	52.00	50.70

X2026WR-2x09B-N0 SN	PA66 UL 94V-0	Brass	Tin-Plated	X2026H-B
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

Wire to board connector

DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X2026WR-2x09B-N0SN
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2026WR-2x09B-N0SN
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

					units: mm
ΔX					tolerance:
ΔX					X.X ±0.2mm
ΔX					X.XX ±0.1mm
MARK					X.XXX ±0.05mm
REVISIONS					UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					