



A




B



TYPE R1

C



TYPE R2

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.02.24	阿树
A2	N/A		产品电气性能变更	2025.12.23	阿树

Specifications:

规格:

Voltage rating:500V AC/DC

额定电压: 500V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+125℃

温度范围: -40℃~+125℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0



材质: PA6T UL94V-0

Plating Category:1U"Gold


镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S



TYPE R1



TYPE R2

PART NO.:

X4611 W V S-14 I-C40 D44 R2
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①Series No

②Category:W-Wafer

③Welding Board Angle:V-Stright 180°

④Welding Way:S-SMT

⑤Row No.Pin No:XX-02~40P

⑥Plastic Height:l=2.0mm

⑦Pin Length:C=4.0mm

⑧Pin Length:D=4.4mm

⑨Type:R1 ; R2

X4611WVS-14I-C40D44R2	PA6T	Brass	X4611F
PART NO	Material	Material(Pin)	Suitable XKB Female

DESIGN

阿树

VIEW:

MODEL TYPE:
2.0mm BTB Connector

CHECKED

UNIT: mm/in

PART NO.:
X4611WVS-14I-C40D44R2

APPROVED

SIZE: A4

DWG NO.:
X-X4611WVS-14I-C40D44R2

SCALE	PAGE	REVISION
N/A	1/1	A2

A

B

C

D