

1

2

3








4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.31	阿 树

A

A

circuit 1
2Pcircuit 1
3Pcircuit 1
4Pcircuit 1
5Pcircuit 1
6P

■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X9357 W R-03-ES N2 SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧



- ① Series No
② Category:W-Wager
③ Welding Board Angle:R-Straight 90°
④ Row No.Pin No:XX-02~06 P
⑤ Special NO:ES-has ears and screw holes
⑥ Material:N2-PA66 UL94V-2
⑦ Plating:SN-Bright tin plating
⑧ Color: Blank-Natural Color

B

B

C

C



Poles	Dimensions(mm)	
	A	B
02	4.20	9.60
03	8.40	13.80
04	12.60	18.00
05	16.80	22.20
06	21.00	26.40

D

D

X9357WR-03ES-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H	1000Pas
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing	Q'ty/Bag

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN
CHECKED
APPROVED阿 树
VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE: 4.20 mm Crimp Style Connectors		
PART NO.: X9357WR-03ES-N2SN		
DWG NO.: X-X9357WR-03ES-N2SN		
SCALE	PAGE	REVISION
N/A	1/1	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4