







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.9.30	



Specifications:


Voltage rating:250V AC/DC
250V AC/DC
Current rating:1A AC/DC
1A AC/DC
Withstanding voltage:1000V AC/minute
1000V AC/
Temperature range:-40 -+125
-40 -+125
Insulation resistance:1000MΩ min
1000MΩ Min
Contact resistance:20mΩ Max
20mΩ Max



PART NO.:

X2003 W V S-XX-LP SN

Series No
Category:W-Wafer
Welding Board Angle:V-Stright 180°
Welding Way: S-SMT
Row No.Pin No:XX-04Pin
Material: LP-LCP UL94V-0
Planting:SN-Tin Plated



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:	MODEL TYPE: 2.00mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X2003WVS-XX-LPSN
APPROVED		SIZE: A4	DWG NO.: