


1

2

3

4

35.00 [1.378]



10.50 [0.413]

5.50 [0.217]

4.50 [0.177] Travel

3.30 [0.130]

3.90 [0.154]



H

0.50 [0.020]

6.70 [0.264]

8.50 [0.335]

1.40 [0.055]

4.50 [0.177]

27.00 [1.063]

XKLBSS Series
6A 125/250VAC**UL** US

2.00 [0.079]

4.50 [0.177]

0.80 [0.031]

PCB LAYOUT

XKLB **UL** US
SS Series
6A 125/250VAC

产品字码标识

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	



规格 Specification:

- 额定值 Rating: 6A 125/250VAC
- 接触电阻 Contact resistance: ≤30 mΩ
- 绝缘电阻 Insulation resistance: ≥100 MΩ(DC500V/Min)
- 电气寿命 Electronics life: >10000 cycles
- 操作力 Operation force: 350±150gf
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X	06	26	P	G-10	N	1	W	W		
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩	⑪

- ① SS: XKB Vertical handle;
② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
③ Current Rating: 06-6A;
④ Switch Circuit: 26-2P6T;
⑤ P: Welding plates;
⑥ Handle Shape: G-Camber handle;
⑦ Handle Height: 3~15mm;
⑧ Enclosure Shape: N-Square enclosure;
⑨ Terminal specs:
1: TYPE-1; 2: TYPE-2; 3: TYPE-3;
4: TYPE-4; 5: TYPE-5;
⑩ Handle Colour:
B-Black; W-White; R-Red
⑪ Housing Colour:
B-Black; W-White; R-Red



CIRCUIT

DESIGN

桑 葚

VIEW:

MODEL TYPE:
SLIDE SWITCH

CHECKED

UNIT: mm/in

PART NO.:
SS-0626PG-10N1WW

APPROVED

SIZE: A4

DWG NO.:
X-SS-0626PG-10N1WW

SCALE

PAGE

REVISION

N/A

1/1

A0

1

2

3

4