





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品图面修正, 图面升级整理图面	2024.08.16	阿 树



Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1.5A AC/DC
额定电流: 1.5A AC/DC
Withstanding voltage:450V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-45℃~+125℃
温度范围: -45℃~+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max


Poles	Dimensions	
	A	B
06	13.34	4.00
08	15.34	6.00
10	17.34	8.00
12	19.34	10.00
14	21.34	12.00
16	23.34	14.00
18	25.34	16.00
20	27.34	18.00
22	29.34	20.00
24	31.34	22.00
26	33.34	24.00
28	35.34	26.00
30	37.34	28.00
32	39.34	30.00
34	41.34	32.00
36	43.34	34.00
40	47.34	38.00
42	49.34	40.00
44	51.34	42.00
50	57.34	48.00
60	67.34	58.00
64	71.34	62.00
68	75.34	66.00



PART NO.:
X2001 W R-2x06 A-6T V01
① ② ③ ④ ⑤ ⑥ ⑦
① Series No
② Category:W-Wafer
③ Welding Board Angle:R-Stright 90°
④ Row No.Pin No:2xXX-2x03-2x32P
⑤ Category:A-No gap
⑥ Material:6T-Nylon 6T UL94V-0
⑦ Plating:V01-Gold Flash

X2001WR-2x06A-6TV01	Nylon 6T	Brass	X2001HA-2xXX
			X2001HA2-2xXX
PART NO	Material	Material(Pin)	Suitable XKB IDC

ANGLAR	±5°
X.	±0.40
X.x	±0.30
*X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	2.0mm Jane cattle 筒牛
PART NO.:	X2001WR-2x06A-6TV01
DWG NO.:	X-X2001WR-2x06A-6TV01