




X9357HF-2x12I-N0

Nylon 66 94V-0

X9357TM

X9357W Or 9357H

Without Ears

PART NO

Material

Suitable XKB Terminal

Suitable XKB Housing

Note

ANGLAR

±5°

X.

±0.40

X.x

±0.30

X.xx

±0.20

X.xxx

±0.15

UNSPECIFIED TOLERANCES

XKB

INDUSTRIAL PRECISION CO.,LIMITED

DESIGN

阿 树

VIEW:

MODEL TYPE:

4.20 mm Crimp Style Connectors

CHECKED

UNIT: mm/in

PART NO.:

X9357HF-2x12I-N0

APPROVED

SIZE: A4

DWG NO.:

X-X9357HF-2x12I-N0

SCALE

PAGE

REVISION

N/A

1/1

A1

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

1

2

3

4