


Rosh

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.15	阿树

带防水圈示意图



U262-164N-4BFC10


1.Au:1U"
4.Au:3U"1:PBT
2:PA6T
3:PA9T
4:LCP
W:WHITE
B:BLACK

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

6	OVER SHELL	STAINLESS STEEL	Ni Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

NOTES: SPECIFICATION:

- 1.CURRENT RATING: 5.0A MAX
- 2.VOLTAGE: 100 VAC
- 3.TEMPERATURE RANGE: -30 °C ~ 85 °C
- 4.CONTACT RESISTANCE: 40 MILLIONHM MAX
- 5.INSULATION RESISTANCE: 100 MEGOHMS MIN.
- 6.INSERTION FORCE : 6N~20N
- 7.UNMATING FORCE: 8N~20N
- 8.DURABILITY: 10,000 CYCLES
- 9.Waterproof rating:IPX6
- 10.Fire rating:UL94V-0



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB 星域
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿树	VIEW:		MODEL TYPE:	USB TYPE C SMT-16PIN PLUG
CHECKED		UNIT:	mm/in	PART NO.:	U262-164N-4BFC10
APPROVED		SIZE:	A4	DWG NO.:	X-U262-164N-4BFC10
		SCALE	PAGE	REVISION	
		N/A	1/1	A1	