






RECOMMENDED P.C.B. LAYOUT (T:1.20~1.60mm)
TOLERANCE UNSPECIFIED ±0.05mm




SPECIFICATIONS

1. OPERATING CURRENT: 0.5A MAX.
2. OPERATION TEMPERATURE: -25°C TO +85°C
3. DIELECTRIC WITHSTANDING VOLTAGE:
500Volts AC BETWEEN ADJACENT TERMINAL (UNMATE)
300Volts AC BETWEEN ADJACENT TERMINAL (MATE)
4. INSULATION RESISTANCE:
100Mohm MIN (UNMATED); 10Mohm MIN. (MATED)
5. HDMI SPECIFICATION COMPLIANCE

A71-05H5-111N1

1: Au 1U"
5: Au 15U"
6: Au 30U"



ROHS COMPLIANCE

3	CONTACTS	19	COPPER ALLOY, GOLD PLATED OVER NICKEL ON CONTACT AREA AND 100u" MIN. TIN PLATED OVER NICKEL ON SOLDER TAILS
2	HOUSING	1	THERMOPLASTIC UL94V-0
1	SHELL	1	COPPER ALLOY, NICKEL PLATED

							DSND		SCALE: N/A	MODEL TYPE: HDMI CONNECTOR			
					ANGLAR	±5°		DWN	VIEW: 	PART NO.: A71-05H5-111N1			
Δx					L≤ 4	±0.2		CHKD	UNIT: mm/in	DWG NO.: A71-05H5-111N1			
Δx					4<L≤ 16	±0.3							
Δx					16<L≤ 63	±0.4							
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5		APPD	SIZE: A4				
REVISIONS							UNSPECIFIED TOLERANCES				XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn											WEIGHT	SHEET	REVISION
												1/1	A0

XKB