






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	①X2	产品尺寸变更，图面升级整理图面	2025.10.18	阿树



PCB LAYOUT

- Specifications(规格):
- 1.Voltage rating(额定电压):DC 12V
 - 2.Current rating(额定电流):0.5A AC/DC
 - 3.Withstanding voltage(耐压值):≥250V AC/minute
 - 4.Insulation resistance(绝缘电阻):≥100MΩ Min
 - 5.Contact resistance(接触电阻):≤30mΩ Max
 - 6.Mating cycles (使用寿命): 50000 cycles Min
 - 7.Travel (行程): 0.35±0.10mm
 - 8.Temperature range(使用温度):-25℃~+70℃

PAPT NO	TC-1103T-B-Y
Operating Force	B:160gf C:260gf
color	B:Black Y: Yellow



CIRCUIT DIAGRAM

A	Pedestal (Housing+Terminal)	1	PPA	Ag-Plating Black
B	Shrapnel	1	SUS	White
C	Button	1	PPA	Black
D	Cover	1	Spcc	White
E	Cards	1	Brass	White
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING/COLOR

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEWS	UNIT: mm/in	MODEL TYPE:	TACT SWITCH
CHECKED		UNIT: mm/in		PART NO.:	TC-1103T-B-Y
APPROVED		SIZE: A4		DWG NO.:	