







2~4 Pin



5~15 Pin

Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:100V AC/minute

耐受电压: 100V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≤100MΩ

绝缘电阻: ≤100MΩ

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X1251 H - 15 - N0

① ② ③ ④

1.Series No

2.Category:H-HSG

3.Row No.Pin No:XX-02~10P

5.Material:N0-Nylon 66 UL94V-0 ;

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.25	3.65	1.90	09	10.00	12.40	6.25
03	2.50	4.90	3.10	10	11.25	13.65	8.20
04	3.75	6.15	4.25	11	12.50	14.90	
05	5.00	7.40	4.25	12	13.75	16.15	
06	6.25	8.65	6.25	13	15.00	17.40	
07	7.50	9.90	6.25	14	16.25	18.65	
08	8.75	11.15	6.25	15	17.50	19.90	

X1251H-15-N0	PA66	AWG#26~30	X1251W	X1251T
PART NO	Material	Wire Range	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X1251H-15-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X1251H-15-N0		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED