








01 Series No.
02 Category:W-wafer
03 Welding Board Angle:R-90°
04 Welding Way: Blank-DIP;
05 Row No.-Pin No.: 2*XX-Double row
06 Special NO.
 s-With positioning column F-halogen free
07 Material:NO-PA6694V-0:N2-PA6694V-2
 LP-LCP 94V-0
08 Planting Category: SN-Bright tin plating 70u"
09 Color: Blank-natural color
 BK-BLACKBL-BLUE RE-RED

Poles	Dimensions(mm)	
	A	B
2*01	---	5.40
2*02	4.20	9.60
2*03	8.40	13.80
2*04	12.60	18.00
2*05	16.80	22.20
2*06	21.00	26.40
2*07	25.20	30.60
2*08	29.40	34.80
2*09	33.60	39.00
2*10	37.80	43.20
2*11	42.00	47.40
2*12	46.20	51.60



	X9357WR-2x02S-LPSN	LCP UL 94V-0	Brass	Tin- Plated	X9357H
	X9357WR-2x02SF-NOSNBK	Nylon 66 UL 94V-0 Halogen Free			
	X9357WR-2x02S-N0SN	Nylon 66 UL 94V-0			
	X9357WR-2x02S-N2SN	Nylon 66 UL 94V-2			
	PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

							XKB	DSND		DATE		SCALE: N/A	MODEL TYPE: 2.40mm Crimp Style Connectors		
Δx				XKB	ANGULAR	$\pm 5^{\circ}$	DWN		DATE		VIEW: 	PART NO.: X9357WR-2x02S-N2SN			
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9357WR-2x02S-N2SN			
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4				
Δx					$16 < L \leq 63$	± 0.4									
MARK	DESCRIPTION			DATE	REVISED	APPROVED									
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT 1.0g	SHEET 1/1	REVISION A0
www.helloxkb.com															