





- ⑨ Color: Blank-natural color

Poles	Dimensions (mm)	
	A	B
02	—	6.65
04	3.00	9.65
06	6.00	12.65
08	9.00	15.65
10	12.00	18.65
12	15.00	21.65
14	18.00	24.65
16	21.00	27.65
18	24.00	30.65
20	27.00	33.65
22	30.00	36.65
24	33.00	39.65

X3025WV-2x10C-LPSN	LCP UL 94V-0	Brass	Tin Plating Fog	X3025H
X3025WV-2x10C-N0SN	Nylon 9T UL 94V-0			
PART NO	Material	Material (Pin)	Finish (Pin)	Mates WithXK B Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors			
				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X3025WV-2x10C-LPSW			
Δx					 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X3025WV-2x10C-LPSW			
Δx					4<L≤16	±0.3	APPD		DATE		SIZE: A4				
Δx					16<L≤63	±0.4									
MARK	DESCRIPTION			DATE	REVISED	APPROVED									
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0
www.helloxkb.com															