







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图面升级整理图面	2024.08.29	阿树



P.C.B Layout

■SPECIFICATIONS

- Voltage rating:50V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ

PART NO.:

X1011 W R S-2x15-9T SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.WELDING Way:S-SMT
- 5.Row No.Pin No:2xXX-2x05~2x25Pin
- 6.Material:9T-PA9T UL94V-0
- 7.Plating:SN-Bright tin plating
V01-All Gold Flash

Poles	Dimensions/mm		
	A	B	C
2x05	4.00	8.10	5.50
2x06	5.00	9.10	6.50
2x08	7.00	11.10	8.50
2x10	9.00	13.10	10.50
2x15	14.00	18.10	15.50
2x20	19.00	23.10	20.50
2x25	24.00	28.10	25.50

X1011WRS-2x15-9TV01	PA9T UL 94V-0	Phosphor Bronze	Gold-Flash	X1011T
X1011WRS-2x15-9TSN			TIN-Plated	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKb Terminal

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 1.0mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.: X1011WRS-2x15-9TSN
APPROVED		SIZE:	A4	DWG NO.: X-X1011WRS-2x15-9TSN

SCALE	PAGE	REVISION
N/A	1/1	A1