


PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C to $+105^{\circ}\text{C}$

温度范围: -40°C to $+105^{\circ}\text{C}$

Insulation resistance: $\geq 500\text{M}\Omega$

绝缘电阻: $\geq 500\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻: $\leq 20\text{m}\Omega$

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U"Gold

镀层: 1U"Gold

Wave soldering temperature: $255 \pm 5^{\circ}\text{C}$, 10S

波峰焊温度: $255 \pm 5^{\circ}\text{C}$, 10S

X1311 F R - 22 - C43 D24

① ② ③ ④ ⑤ ⑥

1. Series No

2. Category: F-Female

3. Welding Board Angle: R-Straight 90°

4. Row No. Pin No: XX-01~40 Pin

5. Plastic height: $C = 4.3\text{mm}$

6. Pin Length: $D = 2.4\text{mm}$

X1311FR-22-C43D24	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR $\pm 5^{\circ}$
ΔX					$L \leq 4$ ± 0.2
ΔX					$4 < L \leq 16$ ± 0.3
ΔX					$16 < L \leq 63$ ± 0.4
ΔX					$L > 63$ ± 0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1311FR-22-C43D24
APPD	SIZE: A4	DWG NO.: X-X1311FR-22-C43D24
WEIGHT		SHEET
		1/1
REVISION		A0