


① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : H-HSG
- ③ Welging Board Angle : F-Female HSG
- ④ Row No.-Pin no.: XX-02P~12P
- ⑤ Plug the Pin & special No. : I-Without Ears
G-With Ears
- ⑥ Material : N2-PA66 94 V-2;
- ⑦ Color: Blank -Natural Color ; WH-White

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.00	6.90	08	21.00	24.90
03	6.00	9.90	09	24.00	27.90
04	9.00	12.90	10	27.00	30.90
05	12.00	15.90	11	30.00	33.90
06	15.00	18.90	12	33.00	36.90
07	18.00	21.90			

X3025HF-10G-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	With Ears
X3025HF-10G-N2WH	Nylon 66 94V-2	White			
X3025HF-10L-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	Without Ears
X3025HF-10L-N2	Nylon 66 94V-2	White			
PART NO	Material	Color	Suitable XKB Terminal	Material With XKB Housing	Note

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
ΔX				XKB	ANGLAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X3025HF-10I-N2		
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025HF-10I-N2		
ΔX					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED								
REVISIONS						UNSPECIFIED TOLERANCES								
www.helloxkb.com						XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT 1.0g	SHEET 1/1	REVISION A0