

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树

Specifications:

规格:

1.Voltage rating:250VAC/DC

额定电压: 250V AC/DC

2.Current rating:3A AC/DC

额定电流: 3A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

4.Temperature range: -55℃~+105℃

温度范围: -55℃~+105℃

5.Insulation resistance:1000MΩ MIN

绝缘电阻:1000MΩ MIN

6.Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

Material:

材料:

7.Rubber core:PBT UL94V-0




胶芯: PBT UL94V-0

8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating

铁壳: SPCC-SD,镀镍/镀锡/镀金

9.Terminal:Copper alloy

端子: 铜合金



NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	18.00	24.99	30.80	19.28
15	26.50	33.32	39.20	27.51
25	40.00	47.04	53.05	41.28
37	56.60	63.50	69.40	57.71

铆合方式	TYPE-1:铆合	TYPE-2:前铆空心螺母	TYPE-3:后铆空心螺母	TYPE-4:后铆空心螺母锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	D-SUB
CHECKED		UNIT:	mm/in	PART NO.:	X0115WT7W1
APPROVED		SIZE:	A4	DWG NO.:	X-X0115WT7W1
SCALE				PAGE	REVISION
N/A				1/1	A1