

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Contact Resistance:≤20MΩ

接触电阻: ≤20MΩ

Insulation Resistance:≥500MΩ

绝缘电阻:≥500MΩ

Dielectric strength:500V AC/minutenai

耐压: 500V AC/minute

X1506 W V S -12-9T SW

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
② Category:W-WAFER
③ Welding Board Angle:V-90°
④ Welding Way:S-SMT
⑤ Row No-Pin No:XX-02-16PIN
⑥ Material:9T-PA9T 94V-0
⑦ Plating Category:SW-Matte Tin Plating(Tin:70u Min)

Poles	Dimensions(mm)			
	A±0.2	B±0.2	C±0.2	D±0.2
2	6.25	2.65	1.50	3.75
3	7.75	4.15	3.00	5.25
4	9.25	5.65	4.50	6.75
5	10.75	7.15	6.00	8.25
6	12.25	8.65	7.50	9.75
7	13.75	10.15	9.00	11.25
8	15.25	11.65	10.50	12.75
9	16.75	13.15	12.00	14.25
10	18.25	14.65	13.50	15.75
11	19.75	16.15	15.00	17.25
12	21.25	17.65	16.50	18.75
13	22.75	19.15	18.00	20.25
14	24.25	20.65	19.50	21.75
15	25.75	22.15	21.00	23.25
16	27.25	23.65	22.50	24.75

X1506WVS-12-9TSW	PA9T UL 94V-0	Brass	Tin-Plated	X1506T
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.50mm Crimp Style Connectors		
DWN		VIEW: 	PART NO.: X1506WVS-12-9TSW		
CHKD		UNIT: mm/in	DWG NO.: X-X1506WVS-12-9TSW		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION						UNSPECIFIED TOLERANCES
REVISIONS						
DATE						
REVISED						
APPROVED						
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB